



Cordless Worklight ML011G / DML817 / ML107



XGT
40V^{max}
LITHIUM-ION

18V
LITHIUM-ION

12V^{max}
LITHIUM-ION

Max luminous flux
ML011G / DML817 | ML107
300 lm | **200 lm**



photo: ML011G



photo: DML817



photo: ML011G



photo: DML817



photo: ML107

ML011G

XGT
40V^{max}
LITHIUM-ION

USB



DML817

18V
LITHIUM-ION

USB



ML107

12V^{max}
LITHIUM-ION

USB






LED light

Daylight white LED
(with color temperature
of 5,000K)

Three lighting modes

Equipped with 2 LEDs, one for sidelighting and the other for uplighting, for wide-angle illumination.



Mode memory function:
The appliance saves the
lighting mode at the time
when turned off by press
and holding the light switch
button.
(This mode is remembered
even if the battery is
removed after that.)


Supplied with Warm white lamp shade

Allowing for changing to warm white tone
lighting (with color temperature of 2,500K),
which has a high relaxing effect



Compact design

Minimal size of the appliance
has been achieved for space
saving use and storage by
designing it on the basis of the
size of compatible battery.



USB output port

ML011G/DML817:
1 port (Type A for DC5V/2.4A)
ML107:
1 port (Type A for DC5V/2.1A)
• With Auto-off function(after
30 minutes of no operation)
• With Output indication lamp



Also can be used for downlighting

With optional "Strap with hook"
fastened to the two Strap holes
on the appliance, the light can
be used for downlighting by
hanging it upside down.



Charging Time

| 40V ^{max} Li-ion | Fast Charging | | 18V LITHIUM-ION | Fast Charging | | 12V ^{max} LITHIUM-ION | Fast Charging | |
|---------------------------|---------------|---------|-----------------|---------------|---------|--------------------------------|---------------|---------|
| | DC40RA | DC40RC | | DC18RC | DC18SD | | DC10SB | DC10WD |
| *1 BL4020 2.0Ah | 22 min | 30 min | BL1815N 1.5Ah | 15 min | 30 min | BL1016 1.5Ah | 22 min | 50 min |
| *1 BL4025 2.5Ah | 28 min | 38 min | BL1820B 2.0Ah | 24 min | 45 min | BL1021B 2.0Ah | 30 min | 70 min |
| *1 BL4040 4.0Ah | 45 min | 67 min | BL1830B 3.0Ah | 22 min | 60 min | BL1041B 4.0Ah | 60 min | 130 min |
| *1 BL4050F 5.0Ah | 50 min | 85 min | BL1840B 4.0Ah | 36 min | 90 min | | | |
| *1 BL4080F 8.0Ah | 76 min | 170 min | BL1850B 5.0Ah | 45 min | 110 min | | | |
| | | | BL1860B 6.0Ah | 55 min | 130 min | | | |

*1 Recommended battery

Accessories

Strap with hook

Part No. SE00001178

Strap with hook is fastened to
the two Strap holes on the
appliance, the light can be used
for downlighting by hanging it
upside down.



Cordless Worklight

ML011G / DML817 / ML107

| | ML011G | DML817 | ML107 |
|--|---|---|---|
| Illuminance (at 0.5 m from the light source) | Sidelighting + Uplighting / Sidelighting only / Uplighting only: 240 / 190 / 190 lx | Sidelighting + Uplighting / Sidelighting only / Uplighting only: 240 / 190 / 190 lx | Sidelighting + Uplighting / Sidelighting only / Uplighting only: 175 / 130 / 130 lx |
| Luminous flux | Sidelighting + Uplighting / Sidelighting only / Uplighting only: 300 / 150 / 150 lm | Sidelighting + Uplighting / Sidelighting only / Uplighting only: 300 / 150 / 150 lm | Sidelighting + Uplighting / Sidelighting only / Uplighting only: 200 / 100 / 100 lm |
| Run time (hrs) | w/ BL4040, at 300 lm: 37 w/ BL4040, at 150 lm: 64 | w/ BL1860B, at 300 lm: 28 w/ BL1860B, at 150 lm: 49 | w/ BL1041B, at 300 lm: 17 w/ BL1041B, at 150 lm: 29 |
| Dimensions (L x W x H) | w/o Battery: 107 x 77 x 50 mm (4-1/4 x 3 x 2") | w/o Battery: 107 x 77 x 50 mm (4-1/4 x 3 x 2") | w/o Battery: 92 x 54 x 47 mm (3-5/8 x 2-1/8 x 1-7/8") |
| Net weight | 0.19 kg (0.42 lbs.) | 0.21 kg (0.46 lbs.) | 0.29 kg (0.13 lbs.) |

Standard Equipment : Warm color cover

not covered by EPTA-Procedure

Items of standard equipment and specifications may vary by country or area.

Makita Corporation

3-11-8 Sumiyoshi-cho, Anjo, Aichi, 446-8502 Japan

PRINTED IN JAPAN 202305